


 Forme
12A2D

 Forme
12V9

 Forme
1A1R

 Forme
90AS

 Forme
1

Programme EWAG - Pierres et meules de réaffutage

Désignation	No article	Forme	Dimensions	Bandeau	Spécification	Granulométrie *
Meule assiette	100708	12A2D	75x22x20	W=3 X=3		B 151
Meule assiette	100302	12A2D	75x22x20	W=3 X=3		B126
Meule assiette	100503	12A2D	75x22x20	W=3 X=3		B54
Meule assiette	100311	12A2D	75x22x20	72X22X20		B46
Meule assiette	100015	12A2D	75x22x20	W=3 X=3		B30
Meule assiette	100301	12A2D	75x22x20	W=3 X=3		B15
Meule assiette	100709	12A2D	75x22x20	W=3 X=3		D10
Meule assiette	100263	12A2D	75x22x20	W=3 X=3		D15
Meule assiette	100710	12A2D	75x22x20	W=3 X=3		D15B
Meule assiette	100013	12A2D	75x22x20	W=3 X=3		D20
Meule assiette	100383	12A2D	75x22x20	W=3 X=3		D7
Meule assiette	100384	12A2D	75x22x20	W=3 X=3		D126
Meule assiette	100711	12A2D	75x22x20	W=3 X=3		D76
Meule assiette	100014	12A2D	75x22x20	W=3 X=3		D46
Meule assiette	100712	12A2D	75x22x20	W=3 X=3		D91
Meule assiette	100713	12A2D	75x22x20	W=3 X=3		D3C50 BCH0
Meule assiette	100714	12A2D	75x22x20	W=3 X=3		D3C50 BCE5
Meule assiette	100715	12A2D	75x22x20	W=6 X=6		D20
Meule assiette	100385	12V9	75x20x20	W=2 X=10		D7
Meule assiette	100386	12V9	75x20x20	W=2 X=10		D20
Meule assiette	100716	12V9	75x20x20	W=2 X=10		D10
Meule assiette	100387	12V9	75x20x20	W=2 X=10		D15
Disque à tronçonner	100717	1A1R	75x0.8x10	U=0.8 X=5		B213
Disque à tronçonner	100388	1A1R	75x0.8x10	U=0.8 X=5		D126
Pierre avivage	100718	90AS	24x13x100		89A 120	
Pierre avivage	100211	90AS	24x13x100		89A 240	
Pierre avivage	100719	90AS	25x13x100		89A 600	
Meule de réaffutage	100725	1	100x10x20		C80	
Meule de réaffutage	100724	1	100x10x20		C120	
Meule de réaffutage	100723	1	100x10x20		C240	
Meule de réaffutage	100127	1	100x10x20		89A120	
Meule de réaffutage	100126	1	100x10x20		89A240	
Meule de réaffutage	100720	1	100x10x20		89A1200	
Meule de réaffutage	100721	1	100x10x20		89A 600	
Meule de réaffutage	100722	1	100x10x20		C600	